

Characteristics

Recessed Compact air curtain, intended for installation in false ceilings. With Kleenfan photocatalysis technology that disinfects and purifies the air, specially designed for commercial doors.



- Kleenfan technology with photocatalytic purificant action fans. UV-A rays, from the
 long-life led, act on the titanium dioxide of the turbine generation Reactive Oxygen
 Species (ROS) than, through oxidation /reduction reactions, inactivate wide range
 of pathogenic microorganisms (viruses and bacteria). It mineralizes most of the
 pollutants present in urban areas produced by vehicles and industry (NOx, SOx,
 COx, formaldehydes, VOCs, etc.).
- Compact and low profile air only recessed air curtain, with full grille view, specially
 designed for applications without heating.
- Self-supporting casing construction made of galvanized steel plate, ready to be installed recessed in a false ceiling.
- Inlet grille (free of maintenance) made with aluminium profiles and blow-out nozzle, integrated in a single white frame colour RAL 9016. Other colours are available on request.
- · Anodized aluminium outlet vanes, airfoil shaped
- EC Double-inlet centrifugal fans driven by an external rotor motor and low noise level, with very low consumption efficency fans.
- "A" type without heating, air only.
- Advanced Plug&Play control. Includes: Advanced PRO control with LCD display and integrated thermostat, door contact, 7m RJ11 cable and remote control. Optional: intelligent Clever Pro Control (automatic, programmable, ModBus for PKC, timer, etc.)

Specifications

50Hz


Unheated					
Model	Nominal Airflow (m³/h)	Recommended Installation Range (m)			
CR ECM 1000 A FC	1840	2,5-3,8			
CR ECM 1500 A FC	2760	2,5-3,8			
CR ECM 2000 A FC	3680	2,5-3,8			
CR ECM 2500 A FC	4600	2,5-3,8			
CR ECG 1000 A FC	2700	3-4,2			
CR ECG 1500 A FC	3600	3-4,2			
CR ECG 2000 A FC	5400	3-4,2			
CR ECG 2500 A FC	6300	3-4,2			


60Hz

Unheated					
Model	Nominal Airflow (m³/h)	Recommended Installation Range (m)			
CR ECM 1000 A FC	1840	2,5-3,8			
CR ECM 1500 A FC	2760	2,5-3,8			
CR ECM 2000 A FC	3680	2,5-3,8			
CR ECM 2500 A FC	4600	2,5-3,8			
CR ECG 1000 A FC	2700	3-4,2			
CR ECG 1500 A FC	3600	3-4,2			
CR ECG 2000 A FC	5400	3-4,2			
CR ECG 2500 A FC	6300	3-4,2			



Dimensions





	L1	Α	В
1000	1048	920	-
1500	1548	1420	710
2000	2048	1920	960
2500	2548	2420	1210

