




Characteristics

Rotowind air curtain for revolving doors and tailor-made with Kleenfan photocatalysis technology that disinfects and purifies the air and cleans it of viruses, bacteria and other pollutants.



Air Disinfection
Performance



- Kleenfan technology with photocatalytic purificant action fans. UV-A rays, from the long-life led, act on the titanium dioxide of the turbine generation Reactive Oxygen Species (ROS) than, through oxidation /reduction reactions, inactivate wide range of pathogenic microorganisms (viruses and bacteria). It mineralizes most of the pollutants present in urban areas produced by vehicles and industry (NOx, SOx, COx, formaldehydes, VOCs, etc.).
- Specially designed to be installed in all type of revolving doors. Two possible layouts, tailored dimensions.
- Self-supporting casing construction made of galvanized steel plate, finished in structural epoxy-polyester painting white colour RAL9016 as standard. Other colours or stainless steel are available on request.
- Large faceted inlet grille avoiding intensive maintenance.
- Circular anodized aluminium outlet vanes, airfoil shaped.
- EC Double-inlet centrifugal fans driven by an external rotor motor and low noise level, with very low consumption efficiency fans.
- “P” type with water heated coil. “E” type with electrical shielded elements, three stages with integrated regulation. “A” type without heating, air only. Optional expansion DX coil.
- Advanced Plug&Play control. Includes: Advanced PRO control with LCD display and integrated thermostat, door contact, 7m RJ11 cable and remote control. Optional: intelligent Clever Pro Control (automatic, programmable, ModBus for PKC, timer, etc.)

Specifications

50Hz

Unheated		
Model	Nominal Airflow (m³/h)	Recommended Installation Range (m)
ROTO ECG 1000 A FC	2700	3-4,2
ROTO ECG 1500 A FC	3600	3-4,2
ROTO ECG 2000 A FC	5400	3-4,2
ROTO ECG 2500 A FC	6300	3-4,2

Electrical Heating			
Model	Nominal Airflow (m³/h)	Electrical Heating Capacity 400Vx3 (kW)	Recommended Installation Range (m)
ROTO ECG 1000 E FC	2700	5/10/15	3-4,2
ROTO ECG 1500 E FC	3600	7,5/15/22,5	3-4,2
ROTO ECG 2000 E FC	5400	10/20/30	3-4,2
ROTO ECG 2500 E FC	6300	10/20/30	3-4,2

Water Heating					
Model	Nominal Airflow (m³/h)	Recommended Installation Range (m)	Heating Capacity 80/60°C (kW) (kW)	Heating Capacity 60/40°C (kW) (kW)	Heating Capacity 50/40°C (kW)
ROTO ECG 1000 P86 FC	2550	3-4,2	11.89	-	-
ROTO ECG 1500 P86 FC	3400	3-4,2	17.29	-	-
ROTO ECG 2000 P86 FC	5100	3-4,2	26.86	-	-
ROTO ECG 2500 P86 FC	5950	3-4,2	33.63	-	-
ROTO ECG 1000 P64 FC	2550	3-4,2	-	11.27	-
ROTO ECG 1500 P64 FC	3400	3-4,2	-	16.77	-
ROTO ECG 2000 P64 FC	5100	3-4,2	-	24.14	-



Water Heating					
Model	Nominal Airflow (m³/h)	Recommended Installation Range (m)	Heating Capacity 80/60°C (kW) (kW)	Heating Capacity 60/40°C (kW) (kW)	Heating Capacity 50/40°C (kW)
ROTO ECG 2500 P64 FC	5950	3-4,2	-	28.84	-
ROTO ECG 1000 P54 FC	2550	3-4,2	-	-	11.5
ROTO ECG 1500 P54 FC	3400	3-4,2	-	-	17.86
ROTO ECG 2000 P54 FC	5100	3-4,2	-	-	25.24
ROTO ECG 2500 P54 FC	5950	3-4,2	-	-	31.38

60Hz

Unheated		
Model	Nominal Airflow (m³/h)	Recommended Installation Range (m)
ROTO ECG 1000 A FC	2700	3-4,2
ROTO ECG 1500 A FC	3600	3-4,2
ROTO ECG 2000 A FC	5400	3-4,2
ROTO ECG 2500 A FC	6300	3-4,2

Electrical Heating			
Model	Nominal Airflow (m³/h)	Electrical Heating Capacity 400Vx3 (kW)	Recommended Installation Range (m)
ROTO ECG 1000 E FC	2700	5/10/15	3-4,2
ROTO ECG 1500 E FC	3600	7,5/15/22,5	3-4,2
ROTO ECG 2000 E FC	5400	10/20/30	3-4,2
ROTO ECG 2500 E FC	6300	10/20/30	3-4,2

Water Heating					
Model	Nominal Airflow (m³/h)	Recommended Installation Range (m)	Heating Capacity 80/60°C (kW) (kW)	Heating Capacity 60/40°C (kW) (kW)	Heating Capacity 50/40°C (kW)
ROTO ECG 1000 P86 FC	2550	3-4,2	11.89	-	-
ROTO ECG 1500 P86 FC	3400	3-4,2	17.29	-	-
ROTO ECG 2000 P86 FC	5100	3-4,2	26.86	-	-
ROTO ECG 2500 P86 FC	5950	3-4,2	33.63	-	-
ROTO ECG 1000 P64 FC	2550	3-4,2	-	11.27	-
ROTO ECG 1500 P64 FC	3400	3-4,2	-	16.77	-
ROTO ECG 2000 P64 FC	5100	3-4,2	-	24.14	-
ROTO ECG 2500 P64 FC	5950	3-4,2	-	28.84	-
ROTO ECG 1000 P54 FC	2550	3-4,2	-	-	11.5
ROTO ECG 1500 P54 FC	3400	3-4,2	-	-	17.86
ROTO ECG 2000 P54 FC	5100	3-4,2	-	-	25.24
ROTO ECG 2500 P54 FC	5950	3-4,2	-	-	31.38



Dimensions

